

# Setaskrib+

*Setaskrib and Setaskrib+ are very practical felt tip pens for drawing on all fabrics, clothing and accessories. Their fine, broad or « brush » points can be used to decorate anything with clear and bright colours or fluorescent colours.*



# Fashion and drawing



## Properties

- Clear vivid and bright colours.
- Fixed with an iron.
- Safety caps.

### Setaskrib+ :

- 18 mixable colours including 6 fluorescent.
- «Brush» points.
- Large reservoir for long-lasting application.
- Conforms to the CE safety standard.

### Setaskrib :

- 12 mixable colours.
- Fine or broad points.
- Conforms to the European toy safety standard 71.3

## APPLICATIONS

Setaskrib and Setaskrib+ felt tip pens for fabrics are particularly practical for decorating T-shirts and cottons and for outlining letters. The different points can be used to produce various lines and effects. All the colours can be mixed together. Using one on top of another, without letting them dry, the colours mix and give superb results. To produce transparent effects, allow the colours to dry between each pass. The colours are superimposed and give watercolour effects. **Setaskrib** and **Setaskrib+** felt tip pens are very easy to use for stencilling, flat tints or producing gradations. Of course, the results depend on the fabric. For example, applied to jersey knit, producing a line pattern, the colours give a pastel or coloured pencil effect. Using **Setaskrib** and **Setaskrib+** felt tip pens is extremely simple and is perfect for teaching children how to paint on silk. First produce a gutta outline, allow to dry and then apply the colour in the patterns, as with a brush.



*Painting on silk.*

Preferably, choose simple shapes and small areas and avoid large single colour backgrounds. **Setaskrib** and **Setaskrib+** can also be used with Pébéo's Setacolor transparent, opaque or pearl colours.






Stencil application.

#### Fixing :

Wait for the colours to dry completely and then fix with an iron, pressing for 2 to 3 minutes on the reverse side of the decorated fabric. Set the temperature to the «cotton» position.




Line patterns.

## RECOMMENDATIONS

Always work on fabric free from sizing. It is recommended that fabric should be washed before applying the colours.

Wait for 48 hours after fixing the colours before washing the decorated fabrics (40°C or 100°F in a washing machine).

This information is given purely for guidance. It is advisable always to perform tests on the bases selected before starting work.




# Setaskrib et Setaskrib+



## Setaskrib+ - 18 colours

- 803 All colours. Box of 6.
- 804 Box of 12 assorted colours.
- 805 Box of 6 assorted fluorescent colours.
- 806 Presentation pack 18 colours x 6.  
Format with decorative front :  
31.5 x 22.5 x 11 cm.




- |                |                       |
|----------------|-----------------------|
| 01 Yellow      | 10 Brown              |
| 02 Orange      | 11 Grey               |
| 03 Red         | 12 Black              |
| 04 Magenta     | 13 Fluorescent yellow |
| 05 Violet      | 14 Fluorescent orange |
| 06 Light blue  | 15 Fluorescent pink   |
| 07 Blue        | 16 Fluorescent violet |
| 08 Light green | 17 Fluorescent blue   |
| 09 Green       | 18 Fluorescent green  |

## Setaskrib - 12 colours

- Broad points**
- 127 All colours. Box of 10.
- 126 Plastic case of 12 assorted colours.
- Fine points**
- 137 All colours. Box of 10.
- 190 Plastic case of 12 assorted colours.
- 128 Plastic case of 6 assorted colours.

## Replacement tips

- 135 Box of 50 broad spare points.
- 625 Box of 50 fine spare points.
- 146 Box of 50 spare caps.



- |                     |                |
|---------------------|----------------|
| 11 Cobalt blue      | 20 Red ochre   |
| 12 Ultramarine blue | 22 Bengal pink |
| 13 Buttercup        | 26 Vermilion   |
| 16 Mouse grey       | 27 Light green |
| 17 Lemon            | 28 Moss green  |
| 19 Black            | 29 Violet      |

Conception - réalisation : NSA - Printed colours may vary from true colours.



Setaskrib : conforms with standard 71.3 - Setaskrib+ : CE - Not intended for use by children under 3. - Labeling conforms to ASTM D-4236 health standard. **Ref. : 6602**

Pébéo (UK) Limited - Unit 416 Solent Business Center - Millbrook Road West - Millbrook/Southampton SO15 OHW - Phone (44) 1703 901914/15 - Fax (44) 1703 901916 - www.pebeo.com

Pébéo of America - Route 78, Airport Road - PO Box 714 - Swanton, VT 05488 - Phone (819) 829 5012 - Fax (819) 821 4151 - www.pebeo.com

Pébéo France - 305, av. du Pic de Bertagne - BP 106 - 13881 Géménos Cedex - France - www.pebeo.com